

760242973 | 360DMiP-24LC-WB

InstaPATCH® 360 LazrSPEED® WideBand Module, 24 LC ports, Lime Green, iPatch Ready



- LazrSPEED® WideBand extends the capability of OM4 across enough spectrum to support at least four low-cost wavelengths

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module

General Specifications

Functionality	Breakout
Adapters, quantity, front	24
Adapters, quantity, rear	2
Color, front	Lime green
Color, rear	Gray
Data Module Type	WideBand
Intelligence Type	iPatch® ready
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Pinned Standard
Shuttered	Yes
Total Fibers, quantity	24
Total Ports, quantity, front	24

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	116.84 mm 4.6 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED® wideband
Insertion Loss Change, mating	0.3 dB
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.47 dB

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)