

760243045 | DM12iP-12LC-WB-ULL



G2 ULL Multimode OM5 MPO-12 Distribution Module, 1x12F MPO unpinned to 12F LC Lime Green, Method B Enhanced, iPatch Ready

Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX ULL

General Specifications

Functionality	Breakout
Adapters, quantity, front	6
Adapters, quantity, rear	1
Color, front	Lime green
Color, rear	Lime green
Data Module Type	G2
Intelligence Type	iPatch® ready
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Shuttered	No
Total Fibers, quantity	12
Total Ports, quantity, front	12

Dimensions

Height	26.42 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	117.35 mm 4.62 in

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

760243045 | DM12iP-12LC-WB-ULL

Fiber Type OM5, LazrSPEED® wideband
Insertion Loss, maximum 0.35 dB

Environmental Specifications

Qualification Standards TIA/EIA-568-C.3
Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system