

CX1247-000 | OCM5-SP11Z00S2-70DASIA



OCM5 Fiber Optic Splitter Module, Planar, one 1x64 Splitter, singlemode, SC/APC, symmetrical split ratio, 7.0 m pigtailed

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM5

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Access	Front
Application	For use with FIST cabinets
Circuits, quantity	1
Distribution Type	1 x 64 splitter
Interface, Input	SC/APC
Interface, Output	SC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	154 mm 6.063 in
Width	16 mm 0.63 in
Depth	142 mm 5.591 in
Pigtail Length, Input	7 m 22.966 ft
Pigtail Length, Output	7 m 22.966 ft

Packaging and Weights

Packaging quantity 1
Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

