

760092023 | RK6-45AM



Equipment Rack, 2-Post, 6 in (152 mm) Channel x 7 ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) M6 Tapped Rails, Black

OBSOLETE

This product was discontinued on: November 30, 2018

Replaced By:

760090134
RK6-45S

Equipment Rack, 2-Post, 6 in (152 mm) Channel x 7 ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	45
Rail Mounting Hole	M6

Dimensions

Height	2,133.6 mm 84 in
Channel Width	152.4 mm 6 in
Width	518.16 mm 20.4 in
Depth	457.2 mm 18 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

760092023 | RK6-45AM

Mechanical Specifications

Static Load Rating 453.6 kg | 1,000.016 lb

Packaging and Weights

Included Four M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

Packaging quantity 1

Packaging Type Flat packed

Weight, net 13.61 kg | 30.005 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

