760109504 | 360G2 Cartridge 12-LCA-SM-GR-PIGTAILS



360G2 Singlemode Fiber Cassette 12 LC APC, with pigtails, iPatch Ready

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber cassette with pigtails

Product Series G2

General Specifications

Color, front Green

Intelligence Type iPatch® ready

Interface, front LC/APC

Interface, rear Stranded pigtail

Total Ports, quantity, front 12

Dimensions

 Height
 25.908 mm | 1.02 in

 Width
 94.996 mm | 3.74 in

 Depth
 123.012 mm | 4.843 in

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A1Insertion Loss, maximum0.34 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Page 1 of 2

760109504 | 360G2 Cartridge 12-LCA-SM-GR-PIGTAILS

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity

Weight, net 0.098 kg | 0.215 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted

