

# 760067157 | PNL-BK-012-MFA-LC02-BG-SHUTTERED



1000-type Adapter Pack, with 6 OptiSPEED® MM duplex LC adapters, beige

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber adapter pack
<b>Product Brand</b>	OptiSPEED®
<b>Product Series</b>	1000-style

## General Specifications

<b>Application</b>	Used in conjunction with G2 1U, 2U and 4U adapter panel shelves, surface mount and raised floor enclosures
<b>Adapter Color</b>	Beige
<b>Adapter Cutout, quantity</b>	12
<b>Adapters, quantity</b>	6
<b>Body Style</b>	Duplex
<b>Interface</b>	LC/UPC
<b>Pigtails Included, quantity</b>	0
<b>Shuttered</b>	Yes

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

760056010 MFA-LC02-BG/LP-SHUTTERED	–	OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack
---------------------------------------	---	--

# 760056010 | MFA-LC02-BG/LP-SHUTTERED



OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber adapter
<b>Product Brand</b>	OptiSPEED®
<b>Product Series</b>	MFA

## General Specifications

<b>Body Style</b>	Duplex
<b>Color</b>	Beige
<b>Interface</b>	LC/UPC
<b>Interface Feature</b>	Reduced footprint
<b>Mounting</b>	No flange
<b>Shuttered</b>	Yes
<b>Total Ports, quantity</b>	2
<b>Transmission Standards</b>	TIA/EIA-568-B.3   TIA/EIA-604 FOCIS-3

## Material Specifications

<b>Alignment Sleeve Material</b>	Phosphorous bronze
----------------------------------	--------------------

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

