

# 760242111 | PNL-CS-24LCV



Standard Density (SD) splicing cassette 24LC OM5, no pigtail

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber cassette  |

## General Specifications

|                                     |            |
|-------------------------------------|------------|
| <b>Adapter Color</b>                | Lime green |
| <b>Interface, front</b>             | LC/UPC     |
| <b>Interface, rear</b>              | No pigtail |
| <b>Total Fibers, quantity</b>       | 24         |
| <b>Total Ports, quantity, front</b> | 12         |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 28.956 mm   1.14 in  |
| <b>Width</b>  | 104.648 mm   4.12 in |
| <b>Depth</b>  | 165.354 mm   6.51 in |

## Optical Specifications

|                   |           |
|-------------------|-----------|
| <b>Fiber Mode</b> | Multimode |
|-------------------|-----------|

## Environmental Specifications

|                        |    |
|------------------------|----|
| <b>Safety Standard</b> | UL |
|------------------------|----|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b> |
|---------------|-----------------------|
|---------------|-----------------------|

# 760242111 | PNL-CS-24LCV

---

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system