



LazrSPEED® Splicing cassette, OM4, 12 LC/UPC , Ribbon

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber cassette with ribbon pigtail |
| Product Brand | LazrSPEED® |

General Specifications

| | |
|-------------------------------------|----------------|
| Adapter Color | Aqua |
| Interface, front | LC/UPC |
| Interface, rear | Ribbon pigtail |
| Total Fibers, quantity | 12 |
| Total Ports, quantity, front | 6 |

Dimensions

| | |
|-----------------------|----------------------|
| Height | 28.956 mm 1.14 in |
| Width | 104.648 mm 4.12 in |
| Depth | 165.354 mm 6.51 in |
| Pigtail Length | 1.5 m 4.921 ft |

Optical Specifications

| | |
|--------------------------------|---------------------|
| Fiber Mode | Multimode |
| Fiber Type | OM4, LazrSPEED® 550 |
| Insertion Loss, typical | 0.3 dB |
| Return Loss, minimum | 25 dB |

Environmental Specifications

| | |
|------------------------|----|
| Safety Standard | UL |
|------------------------|----|

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

