


# FSXLCLCWM

---

## Base Product



LazrSPEED® 550 LC/UPC to LC/UPC, Distribution Cable, 144-Fiber, Plenum

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber distribution cable assembly
<b>Product Brand</b>	SYSTIMAX InstaPATCH® 360
<b>Ordering Note</b>	For lengths greater than 999 ft (304 m), orders must be in meters

## General Specifications


<b>Cable Glands</b>	No glands
<b>Color, connector A</b>	Black
<b>Color, connector B</b>	Black
<b>Construction Type</b>	Distribution, indoor
<b>Interface, Connector A</b>	LC/UPC
<b>Interface, Connector B</b>	LC/UPC
<b>Total Fibers, quantity</b>	144

## Dimensions

<b>Cable Assembly Length Range (m)</b>	3 – 999
<b>Cable Assembly Length Range (ft)</b>	10 – 999

## Ordering Tree

# FSXLCLCWM



## Mechanical Specifications

**Cable Retention Strength, maximum** 0.50 lb @ 0° | 0.50 lb @ 90°

## Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM4, LazrSPEED®

## Environmental Specifications

**Operating Temperature** 0 °C to +70 °C (+32 °F to +158 °F)

**Environmental Space** Indoor | Plenum

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# FSXLCLCWM

---

## Included Products

- 460125271 – Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode
- P-144-DS-5K-FMU – Fiber indoor cable, LazrSPEED® Plenum Distribution, 144-Fiber Multi-Unit with 12-Fiber Subunits, Multimode OM4, Gel-free, Feet jacket marking