
## U4GLGLGCG

#### **Base Product**



Ultra Low Loss ULL TeraSPEED® LC/APC G B to LC/APC G B Ruggedized fanout Cable, 36-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

### General Specifications

Color, boot A Green

Color, connector A Green

Color, boot B Green

Color, connector B Green

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A LC/APC

Interface Feature, connector A Grade B performance

Interface, Connector B LC/APC

Interface Feature, connector B Grade B performance

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 36

. . ,

**Dimensions** 

Cable Assembly Length Range (m) 3 – 999

COMMSC PE®

# U4GLGLGCG

Cable Assembly Length Range (ft) 8 – 999

Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

**Environmental Specifications** 

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (+14 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





