

R4-PNFNF-7M

RCT4, Radiax Radiating® Jumper with interface types N Female and N Female, 7m



Product Classification

| | |
|-----------------------|--------------------------------------|
| Product Type | Wireless transmission cable assembly |
| Product Brand | RADIAX® |
| Product Series | RCT4 |

General Specifications

| | |
|---|----------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | N Female |
| Interface, Connector B | N Female |
| Orientation | 180° |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 7 m 22.966 ft |
| Nominal Size | 1/2 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 800–2700 MHz | 1.288 | 18 |

Jumper Assembly Sample Label

R4-PNFNF-7M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |