



Carrier Access Point with 4-Band Support for High Power LMR 750, USA 700, USA 750, SMR 800, CEL 850, AWS 1700 and PCS 1900 Applications, Fiber Fed with Fan Kit

Product Classification

Regional Availability	North America
Product Type	Access point
Product Brand	ERA®
Product Series	CAP H

General Specifications

Fan Kit	Included
Fed Type	Fiber fed
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	High
Powering Type	Internal DC powered

Electrical Specifications

License Band	AWS 1700 CEL 850 LMR 750 PCS 1900 SMR 800 USA 700 USA 750
Voltage Range	-57 to -42 Vdc