



Carrier Access Point for High Power for EGSM-R Applications, Fiber Fed with Fan Kit

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Access point
<b>Product Brand</b>	ERA®
<b>Product Series</b>	CAP H

## General Specifications

<b>Fan Kit</b>	Included
<b>Fed Type</b>	Fiber fed
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Power Class</b>	High
<b>Powering Type</b>	Internal AC powered

## Electrical Specifications

<b>License Band</b>	GSM-R
<b>Voltage Range</b>	100 to 240 Vac

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

