

UA-3G



Galvanized Steel Angle Adapter, universal, snap-in, 3/4 in through hole

Product Classification

Product Type	Adapter
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Angle adapter
Mounting	3/4 in through hole

Dimensions

Inside Width	22.352 mm 0.88 in
Outside Width	57.15 mm 2.25 in
Inside Length	25.4 mm 1 in
Outside Length	50.8 mm 2 in
Material Thickness	2.667 mm 0.105 in

Material Specifications

Material Type	Galvanized steel
----------------------	------------------

Mechanical Specifications

Installation Torque, maximum	15 ft lb 20.337 N-m
Installation Torque, minimum	11 ft lb 14.914 N-m
Maximum Loading	Triple stack, 1-5/8 in cable

Packaging and Weights

Height, packed	25 cm 9.843 in
Width, packed	14 cm 5.512 in
Length, packed	12 cm 4.724 in

UA-3G

Packaging quantity 10
Weight, gross 2.32 kg | 5.115 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

