

# LSX-7L/OLA023

---



LSX Fiber Termination Chassis 4 RU, 96 - SC/APC, Singlemode IFC Ribbon, 23 Meters, Far end connection Stub

## Product Classification

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Regional Availability</b> | Latin America   North America       |
| <b>Portfolio</b>             | CommScope®                          |
| <b>Product Type</b>          | Fiber patch chassis, with IFC cable |
| <b>Product Series</b>        | LSX                                 |

## General Specifications

|                              |                               |
|------------------------------|-------------------------------|
| <b>Functionality</b>         | Patching                      |
| <b>Application</b>           | Used in LSX-style frames only |
| <b>Cable Exit Location</b>   | Upward                        |
| <b>Cable Stub Type</b>       | IFC, ribbon                   |
| <b>Color</b>                 | Putty white                   |
| <b>Growth Configuration</b>  | Fully loaded                  |
| <b>Interface, front</b>      | SC/APC                        |
| <b>Interface, rear</b>       | Stub tail                     |
| <b>Rack Type</b>             | EIA 19 in   EIA 23 in         |
| <b>Rack Units</b>            | 4                             |
| <b>Shelf Movement</b>        | Fixed                         |
| <b>Total Ports, quantity</b> | 96                            |

## Dimensions

|                     |                  |
|---------------------|------------------|
| <b>Height</b>       | 177.8 mm   7 in  |
| <b>Width</b>        | 482.6 mm   19 in |
| <b>Depth</b>        | 304.8 mm   12 in |
| <b>Cable Length</b> | 23 m   75.459 ft |

# LSX-7L/OLA023

---

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

