



ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
1	CL10.01	10' ANGLE SIDE RAIL	2	16.37 LBS
2	CL09R.01	29" LADDER RUNG	3	2.48 LBS
3	HKCLU.02	BACKING PLATE	4	0.95 LBS
4	GB-03145	3/8" X 1-1/2" GALV BOLT KIT	10	0.07 LBS
5	GJB0380	8" GALV J-BOLT KIT	4	0.23 LBS
6	GWF-03	3/8" GALV FLAT WASHER	8	0.01 LBS
7	GWL-03	3/8" GALV LOCK WASHER	4	0.00 LBS
8	GN-03	3/8" GALV HEX NUT	4	0.01 LBS

REVISIONS				
REV.	ZONE	DESCRIPTION	BY	DATE
A		INITIAL RELEASE	ACG	01/14/06
B		REPLACE J-BOLT FROM JB-HK	ACG	12/11/08
C		UPDATE BOM	MSM	05/15/13



ANGLE MEMBER SET-UP

ROUND MEMBER SET-UP



DETAIL A SCALE 1 : 6

DETAIL B SCALE 1 : 6

NOTES:  
1. ALL METRIC DIMENSIONS ARE IN BRACKETS.

These drawings and specifications are the proprietary property of CommScope Inc. and may be used only for the specific purpose authorized in writing by CommScope Inc.

ALL DIMENSIONS ARE IN INCHES U.O.S.  
TOLERANCES UNLESS OTHERWISE SPECIFIED:  
.X = ± .12 ANGLES ±2°  
.XX = ± .06 FRACTIONS ±1/32  
.XXX = ± .03

REMOVE BURRS AND BREAK EDGES .005

DO NOT SCALE THIS PRINT

DRAWN BY: ACG	SHEET: 1 of 1	PART NUMBER: CL-0910-U
CHECKED BY: TP	SCALE: NTS	DESCRIPTION: 10' CABLE LADDER - 9 HOLE RUNGS
DATE: 01/14/06	MATERIAL: A36, A529	DRAWING TYPE: ASSEMBLY DRAWING
REVISION: C	FINISH: GALV A123	 Hickory, NC 28602 U.S.A.
	WEIGHT: 45.98 LBS	