

760154120 | H61A-317-RED

High Density Icon Strip, red, bulk pack



OBSOLETE

Replaced By:

760164434
H61K-ICON-RD

HGS620 Icon Strip (Voice / Data / Blank), Red (25 ea/pkg)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Icon kit
Ordering Note	Minimum order quantity, 20 packs

General Specifications

Color Red

Dimensions

Height 13.97 mm | 0.55 in

Width 23.62 mm | 0.93 in

Depth 2.79 mm | 0.11 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

760154120 | H61A-317-RED

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 25

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

