

760181743 | M10L-266

M10L-266 Faceplate, pro white

OBSOLETE

Replaced By:

760249144
FP-LBL-1P-266 Faceplate Kit, Labelled, 1-gang, 1 port, pro white

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Faceplate kit
Product Series	M Series

General Specifications

Application	Used with M Series modular information outlet
Color	Pro white
Mounting	Flush
Total Ports, quantity	1

Dimensions

Height	115.824 mm 4.56 in
Width	71.374 mm 2.81 in
Depth	7.366 mm 0.29 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity 1
Weight, net 0.036 kg | 0.08 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

