

# CC8313-000 | OCC1P-16400-NNNQNF



OCC1P Wideband Splitter, planar, singlemode, 1 x 64, symmetrical split ratio, 0,250 mm cable, field installable

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Splitter component
<b>Product Series</b>	OCC1P
<b>Government Requirements</b>	Build America Buy America (BABA) compliant*

## General Specifications

<b>Device Type</b>	Component, rectangular
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 64 splitter
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail
<b>Location of Manufacturing</b>	Waived per BABA waiver for BEAD Program
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Pigtail Length, Input</b>	2.5 m   8.202 ft
<b>Pigtail Length, Output</b>	2.5 m   8.202 ft
<b>Pigtail Diameter, Input</b>	0.25 mm   0.01 in
<b>Pigtail Diameter, Output</b>	0.25 mm   0.01 in

## Environmental Specifications

<b>Qualification Standards</b>	Telcordia GR-1209-CORE   Telcordia GR-1221-CORE
--------------------------------	-------------------------------------------------

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

