

760249308 | CPP-IP-6A-STP-1U-24



CommScope® imVision® STP Cat 6A Modular Panel, 24 port

Product Classification

Regional Availability	Asia EMEA
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Brand	imVision®

General Specifications

ANSI/TIA Category	6A
Cable Type	Shielded
Color	Silver
Intelligence Type	iPatch® enabled
Panel Style	Straight
Rack Units	1
Total Ports, quantity	24
Wiring	T568A T568B

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	206.5 mm 8.13 in
Compatible Diameter Over Dielectric, maximum	1.168 mm 0.046 in

Electrical Specifications

Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Mechanical Specifications

760249308 | CPP-IP-6A-STP-1U-24

Plug Insertion Life, minimum

750 times

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Safety Standard

UL | cUL

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant/Exempted

