

# FGS-MSHS-M12

---



FiberGuide® Horizontal Straight Section, 4x18 in, 12ft Long, Yellow

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Straight section
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Color</b>	Yellow
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Straight section

## Dimensions

<b>Height</b>	118.593 mm   4.669 in
<b>Length</b>	3,657.6 mm   144 in
<b>System Dimensions</b>	102 mm x 457 mm (4 in x 18 in)

## Material Specifications

<b>Material Type</b>	Engineering Thermoplastic
----------------------	---------------------------

## Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

## Packaging and Weights

<b>Weight, net</b>	17.869 kg   39.394 lb
--------------------	-----------------------

# FGS-MSHS-M12

---

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

