



4 in boot cushion insert with 1 hole for HELIAX® cables (Fusion tape included)

Product Classification

Product Type	Cushion insert
Product Brand	I-Line
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Hybrid fiber
Cables per Cushion	1
Color	Black

Dimensions

Height	82.55 mm 3.25 in
Length	25.4 mm 1 in
Nominal Size	1-1/4 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packaging and Weights

Height, packed	170.18 mm 6.7 in
Width, packed	129.54 mm 5.1 in
Length, packed	99.06 mm 3.9 in
Included	Cushion

294701-T

Packaging quantity 1
Weight, gross 0.5 kg | 1.102 lb

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Included Products

FT-TB – Black Self-fusing Tape, 15 ft

FT-TB



Black Self-fusing Tape, 15 ft

Product Classification

Product Type	Weatherproofing tape
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Application	Provides additional moisture seal for cable connections
Applications per Kit	Four 1/2 in–1/2 in One 1/2 in–2-1/4 in Two 1/2 in–7/8 in Two 1/2 in–7/8 in to device
Color	Black

Dimensions

Width	38.1 mm 1.5 in
Length	4572 mm 180 in
Nominal Size	1-1/4 in 1-5/8 in 1/2 in 1/4 in 2-1/4 in 3/8 in 5/8 in 7/8 in

Material Specifications

Material Type	Silicone tape
----------------------	---------------

Environmental Specifications

UV Resistance Test Method	ASTM D518, Test Method B
Weather Resistance Test Method	04AS00-03.6.0 MIL-STD-1344A, Method 1002

Packaging and Weights

Height, packed	83.82 mm 3.3 in
Width, packed	83.82 mm 3.3 in
Length, packed	5.08 mm 0.2 in
Packaging quantity	2

FT-TB

Weight, gross

0.1 kg | 0.22 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

