

BHD-38



Double Block Hanger for 3/8 in coaxial cable - Hardware Sold Separately
(search 243095-SERIES-HARDWARE for options available)

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Double block hanger
Mounting	Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

Dimensions

Maximum Stack Height	4
Height	36.1 mm 1.421 in
Width	24.1 mm 0.949 in
Length	42.9 mm 1.689 in
Compatible Cable Diameter Range	10–12 mm
Compatible Diameter, maximum	12 mm 0.472 in
Compatible Diameter, minimum	10 mm 0.394 in
Nominal Size	3/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

BHD-38

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	3.8 cm 1.496 in
Width, packed	12.7 cm 5 in
Length, packed	17.8 cm 7.008 in
Packaging quantity	10
Weight, gross	0.14 kg 0.309 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power