

FA-3540-STH



Standard Butterfly Hanger and Grommet kit for HELIAX® Cables, 35-40mm

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®

General Specifications

Cables per Hanger	1
Color	Black Silver
Hanger Type	Hanger kits
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Height	51.1 mm 2.012 in
Compatible Diameter, maximum	40 mm 1.575 in
Compatible Diameter, minimum	35 mm 1.378 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	EPDM rubber Stainless steel
----------------------	-------------------------------

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

FA-3540-STH

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight

Packaging and Weights

Height, packed	26 cm 10.236 in
Width, packed	9 cm 3.543 in
Length, packed	9 cm 3.543 in
Packaging quantity	10
Weight, gross	0.53 kg 1.168 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

