

# MWH-1-58-Y

---



## Messenger Wire Hanger for 1-5/8 in RADIAX® Radiating Cable

### OBSOLETE

This product was discontinued on: December 30, 2024

## Product Classification

**Product Type** Hanger kit

## General Specifications

**Cables per Hanger** 1  
**Color** Black  
**Hanger Type** Hanger kits

## Dimensions

**Height** 123.4 mm | 4.858 in  
**Width** 50.5 mm | 1.988 in  
**Length** 65 mm | 2.559 in  
**Compatible Diameter, maximum** 50.5 mm | 1.988 in  
**Compatible Diameter, minimum** 46.5 mm | 1.831 in  
**Diameter Over Messenger Wire, maximum** 9 mm | 0.354 in  
**Diameter Over Messenger Wire, minimum** 6 mm | 0.236 in  
**Nominal Size** 1-5/8 in

## Material Specifications

**Material Type** Polyamide PA66

## Mechanical Specifications

**Maximum Load** 3500 N | 786.832 lbf

# MWH-1-58-Y

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Flammability Test Method</b>	UL 94 V-0
<b>Toxicity Index Test Method</b>	IEC 60754-2
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours

## Packaging and Weights

<b>Height, packed</b>	28 cm   11.024 in
<b>Width, packed</b>	23 cm   9.055 in
<b>Length, packed</b>	26 cm   10.236 in
<b>Packaging quantity</b>	50
<b>Weight, gross</b>	4.8 kg   10.582 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

