MHD-FFDH



Hardened Multifiber Optical Connector (HMFOC) cable assembly, HMFOC plug HMFOC plug, 12-fiber

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Hardened drop cables incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability

Asia | Latin America | North America

Product Type Fiber drop cable assembly

Product Series MHD

General Specifications

Cable Type Toneable - Flat

Connector A, quantity 1

Color, boot ABlackColor, connector ABlackConnector B, quantity1

Color, boot B Black
Color, connector B Black

Interface, Connector A Hardened multi-fiber (HMFOC) plug

Interface Feature, connector A Female | Unpinned

Interface, Connector B Hardened multi-fiber (HMFOC) plug

Interface Feature, connector B Female | Unpinned

Jacket Color Black
Total Fibers, quantity 12

Dimensions

Cable Assembly Length Range (m) 8 - 915


Cable Assembly Length Range (ft) 25 - 3000

Cable Outer Diameter 4.3 x 9.9 mm (0.17 x 0.39 in)

COMMSC PE®


MHD-FFDH

Ordering Tree



^{*} Cable Length shown as an example, additional cable lengths available upon request up to 2,000 ft. (600 m).

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded86 mm | 3.386 inMinimum Bend Radius, unloaded81 mm | 3.189 inTensile Load, long term, maximum400 N | 89.924 lbfTensile Load, short term, maximum1334 N | 299.895 lbf

Optical Specifications

Fiber Mode Singlemode

COMMSCOPE®

MHD-FFDH

Fiber Type G.657.A2, TeraSPEED®

Insertion Loss, maximum, connector A0.45 dBInsertion Loss, maximum, connector B0.45 dBReturn Loss, minimum, connector A65 dBReturn Loss, minimum, connector B65 dB

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-22 °F to} + 158 °F)$ Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-40 °F to} + 158 °F)$ Storage Temperature $-40 \,^{\circ}\text{C to} + 75 \,^{\circ}\text{C (-40 °F to} + 167 °F)$

Environmental Space Outdoor, buried

Jacket UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

810009374/DB O-012-DF-HY-F12NS/30T Tone Wire Outdoor Drop Cable, 12 fiber Arid Core construction, central loose tube

