

SSH-114-3



SnapStak® Hanger for 1-1/4 in coaxial cable, triple stack capability, includes reinforcement bar

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	40.9 mm 1.61 in
Width	40.1 mm 1.579 in
Length	81 mm 3.189 in
Compatible Cable Diameter Range	37.6–43.2 mm
Compatible Diameter, maximum	43.2 mm 1.701 in
Compatible Diameter, minimum	37.6 mm 1.48 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

SSH-114-3

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Double cable weight

Packaging and Weights

Height, packed

22 cm | 8.661 in

Width, packed

14.6 cm | 5.748 in

Length, packed

14.8 cm | 5.827 in

Packaging quantity

10

Weight, gross

0.52 kg | 1.146 lb

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power