

NG4-CMDKNHQ



NG4access® Cabled Module, singlemode LC/UPC module at both sides, 144 fiber, stranded, IFC

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber cabled module |
| Product Brand | NG4access® |
| Product Series | LSX NG4 |
| Ordering Note | For fiber modules with custom cable lengths, please contact your local CommScope representative |

General Specifications


| | |
|-------------------------------------|--------------------------|
| Configuration Type | NG4 Module to NG4 Module |
| Adapters, quantity, front | 72 |
| Body Style | Straight orientation |
| Cable Color | Yellow |
| Cable Type | IFC - Stranded |
| Color, front | Black |
| Color, housing | Black |
| Color, rear | Black |
| Interface, front | LC/UPC |
| Interface, rear | LC/UPC |
| Polarity | Pairs, straight |
| Total Fibers, quantity | 144 |
| Total Ports, quantity, front | 144 |

NG4-CMDKNHQ

Dimensions

| | |
|---------------|---------------------|
| Height | 13.3 mm 0.524 in |
| Width | 159.9 mm 6.295 in |
| Depth | 101 mm 3.976 in |

Ordering Tree



Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A2 |

Environmental Specifications

| | |
|----------------------------|--------------------------------------|
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
|----------------------------|--------------------------------------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

NG4-CMDKNHQ

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

