

760250320 | CPPA-UDDM-KJ-2U-48-WH



Unshielded Angled Discrete Distribution Module Panel, Keystone, 2U, 48 port, White

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Series	KJ Series

General Specifications

Application	For use with Keystone outlets
Cable Type	Unshielded
Color	White
Panel Style	Angled
Rack Type	EIA 19 in
Rack Units	2
Total Ports, quantity	48
Wiring	T568A T568B

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth, with cable management	210.82 mm 8.3 in

Electrical Specifications

Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-
----------------------	---

760250320 | CPPA-UDDM-KJ-2U-48-WH

coated steel

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	RCM UL cUL

Packaging and Weights

Packaging Material	Eco-friendly, single-use plastics-free
Packaging quantity	1