

F1A-HMHM-W-CC

FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Nominal Size	1/4 in
---------------------	--------

Electrical Specifications

3rd Order IMD Static	-107 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers

Jumper Assembly Sample Label

F1A-HMHM-W-CC



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition