

# VSRC-MM-1550

---



Interlocking Channel V-Stabilizer™ for a Monopole - Adjustable from 34.5" to 57.5" Plus Vertical & Horizontal Adjustments

## Product Classification

**Product Type** Reinforcement kit

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Length** 1,460.5 mm | 57.5 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Legs | Ring mount

**Packaging quantity** 1

**Weight, net** 162.182 kg | 357.55 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

