

# RT-NF10-4-126

---



High Capacity Non-Penetrating Roof Frame, 10 ft face, Four 2-7/8 in OD x 126 in pipes

## Product Classification

**Product Type** Non-penetrating roof frame

## General Specifications

**Mounting** Non-penetrating

**Pipe, quantity** 4

## Dimensions

**Height** 3,200.4 mm | 126 in

**Face Width** 3.2 m | 10.5 ft

**Width** 3,200.4 mm | 126 in

**Length** 2.377 m | 7.8 ft

**Pipe Length** 3,200.4 mm | 126 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

**Pipe Outer Diameter** 73.152 mm | 2.88 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Ballast tray | Frame | Plain end pipes (4)

## Regulatory Compliance/Certifications

# RT-NF10-4-126

---

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

