# UJGQPQXTH

#### **Base Product**



Ultra Low Loss (ULL) Singlemode MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 48-Fiber, Dual Rated (OFNR /LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

#### General Specifications

Connector A, quantity 6

Color, boot A Gray

Color, connector A Green

Connector B, quantity 6

Color, boot B Gray

Color, connector B Aqua

**Construction Type** Stranded

Furcation Color Yellow

Interface, Connector A MPO-08/APC Female

Interface, Connector B MPO-08/APC Male

**Jacket Color** Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 48

Dimensions

Breakout Length 22 in


**COMMSCOPE®** 

# UJGQPQXTH

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

### **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



**COMMSCOPE®** 

# UJGQPQXTH

#### Included Products

760245573 N-048-MP-8G1-F08YL/20T/D

Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with 8 fiber 2.0 mm subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame

MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm 860659022 MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm 860659028

