


# UQGRXR7R

Base Product



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Pinned) to MPO16 (Pinned), Fiber Array Cable Assembly, 16-Fiber, Plenum

## Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America   |
| <b>Portfolio</b>             | CommScope®   |
| <b>Product Type</b>          | Fiber array cable assembly   |
| <b>Product Brand</b>         | Propel   SYSTIMAX ULL  |
| <b>Ordering Note</b>         | For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration |

## General Specifications

|                                     |                         |
|-------------------------------------|-------------------------|
| <b>Connector A, quantity</b>        | 1                       |
| <b>Color, boot A</b>                | Black                   |
| <b>Color, connector A</b>           | Green                   |
| <b>Connector B, quantity</b>        | 1                       |
| <b>Color, boot B</b>                | Black                   |
| <b>Color, connector B</b>           | Green                   |
| <b>Construction Type</b>            | Stranded                |
| <b>Furcation Color</b>              | Yellow                  |
| <b>Interface, Connector A</b>       | MPO-16/APC Male         |
| <b>Interface, Connector B</b>       | MPO-16/APC Male         |
| <b>Jacket Color</b>                 | Yellow                  |
| <b>Polarity</b>                     | Method B Enhanced (ULL) |
| <b>Fibers per Subunit, quantity</b> | 16                      |
| <b>Total Fibers, quantity</b>       | 16                      |

## Dimensions


|  |         |
|--|---------|
| <b>Cable Assembly Length Range (m)</b> | 1 – 305 |
|--|---------|

# UQGRXR7R

Cable Assembly Length Range (ft)

1 – 999

## Ordering Tree



## Mechanical Specifications

**Cable Retention Strength, maximum** 11.24 lb @ 0 ° | 4.40 lb @ 90 °

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Indoor | Plenum

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

- 760249691 P-016-MP-8G1-F30YL – Fiber indoor cable, Plenum MPO Light Duty for Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

# UQGRXR7R

---

860661398

– Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable