

C112LNSG



Waveguide/Coaxial Cable Transition for WR112, 7.05–10.0 GHz, with interface types N Female and UDR84, gray

Product Classification

Product Type Waveguide/Coaxial Cable Transition

General Specifications

Component Waveguide/Coaxial Cable Transition

Interface N Female

Interface 2 UDR84

Dimensions

Waveguide Size WR112 | WG15 | R84

Electrical Specifications

Operating Frequency Band 7.05 – 10.0 GHz

VSWR 1.1

Material Specifications

Finish Gray

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

