NG4-CMDKPGQ



NG4access® Cabled Module, singlemode LC/UPC to MPO/APC, 72 fiber, stranded, IFC

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber cabled module
Product Brand	NG4access®
Product Series	LSX NG4
Ordering Note	For fiber modules with custom cable lengths, please contact your local CommScope representative

General Specifications

Configuration Type	NG4 Module to MPO Connector
Adapters, quantity, front	36
Body Style	Straight orientation
Cable Color	Yellow
Cable Type	IFC - Stranded
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	MPO-12/APC Female
Interface Feature, rear	Female
Polarity	Pairs, straight
Total Fibers, quantity	72
Total Ports, quantity, front	72


Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 16, 2024



NG4-CMDKPGQ

Ordering Tree



Optical Specifications

Fiber Mode	Singlemode	
Fiber Type	G.657.A2	

Environmental Specifications

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity	1
r dokaging quantity	1

Page	2	of	2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 16, 2024

