


D112CCSG



90° Rigid Twist for WR112, 7.05–10.0 GHz, with interface types CPR112G and CPR112G, 10 in, gray

Product Classification

Product Type Rectangular waveguide, rigid twist

General Specifications

Component 90° Rigid Twist

Interface CPR112G

Interface 2 CPR112G

Dimensions

Length 254 mm | 10 in

Waveguide Size WR112 | WG15 | R84

Electrical Specifications

Operating Frequency Band 7.05 – 10.0 GHz

VSWR 1.06

Material Specifications

Finish Gray

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system