



Wall Mountable Fiber Endclosure including 2 LC/APC (duplex) adapters and 4 900 μ pigtails, feeder cable can be stored up to 50m depending on cable diameter, cable cover not included

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber wall box
Product Series	WMFE

General Specifications

Adapter Ports, quantity	
Adapters, quantity	2
Cable Entry Location	Bottom
Color	Light Gray (RAL 7035)
Interface	LC/APC
Mounting	Wall mount
Patch Cord Routing	Downward
Patching Capacity, maximum	4
Splicing Capacity, maximum	4
Splicing Type	SMOUV

Dimensions

Height	196 mm 7.717 in
Height, with cover	mm 11.063 in
Width	154 mm 6.063 in
Depth	43 mm 1.693 in
Outer Cable Diameter	10 mm 0.394 in

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

UV Resistance UV stabilized

Packaging and Weights

Height, packed 44 mm | 1.732 in
Width, packed 156 mm | 6.142 in
Depth, packed 286 mm | 11.26 in
Packaging quantity 24
Packaging Type Carton
Weight, gross 0.513 kg | 1.131 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

