

4

3

2

1

NOTES:

1.0 GENERAL  
 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS  
 2.0 DESIGN NOTES  
 2.1 DESIGNED PER CUSTOMER REQUIREMENTS  
 2.2 WILL FIT 12" - 45" MONOPOLE  
 3.0 MANUFACTURING/SPECIAL REQUIREMENTS  
 4.0 TEST  
 5.0 PACKAGING

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	8000040262	INITIAL RELEASE	MRC	05/28/20

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE X ± .25	2 PLACE .XX ± 0.06	VZWSMART-PLK7	
1 PLACE .X ± 0.12	ANGLES ± 2°		
FINISH GALV A123		MATERIAL A1011/A1018, A500,A529	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	CE	MRC	05/28/20	TITLE <b>MONOPOLE COLLAR MOUNT ASSEMBLY</b>					
	RW	MC1107	07/23/2020						
	RV								
	AD	BCAMPBELLCON	08/07/2020						
RE	BCROSS	08/07/2020		SCALE <b>1:4</b>					
ECN 008000040262				DOCUMENT NO. <b>VZWSMART-PLK7</b>					
SIZE	WORK AREA	24	MODEL						
<b>C</b>			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	SHEET 1 OF 1
			01	RE		01	RE		

DENSITY		lbs/in <sup>3</sup>
MASS	104.17	lbs
VOLUME	521.54	in <sup>3</sup>
SURFACE AREA	4659.69	in <sup>2</sup>
HEIGHT		
LENGTH		
WIDTH		

© 2020 CommScope, Inc.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	MTC4104-0100	WELDMENT, RINGMOUNT 12"-45"	3
2	MT38248	5/8" X 48" GALV THREADED ROD	6
3	GWL-05	5/8" GALV LOCK WASHER	12
4	GN-05	5/8" GALV HEX NUT	12
6	GWF05A	GALV FLAT WASHER HARDENED 5/8", 1.30D	12

4

3

2

1