

# RT-SF7-3-96

---



High Capacity Penetrating Roof Frame, 7 ft face, three 2-7/8 in OD x 96 in pipes

## Product Classification

**Product Type** Rooftop sector frame

## General Specifications

**Mounting** Penetrating

**Pipe, quantity** 3

## Dimensions

**Height** 2,438.4 mm | 96 in

**Face Width** 2,286 mm | 7.5 ft

**Width** 2,286 mm | 90 in

**Length** 1,311 mm | 4.3 ft

**Pipe Length** 2,438.4 mm | 96 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

**Pipe Outer Diameter** 73.152 mm | 2.88 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Frame | Plain end pipes

## Regulatory Compliance/Certifications

# RT-SF7-3-96

---

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

