

F1A-HFKM-P-W1

Base Product



FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Female and 4.1-9.5 DIN Male with HELIAX® SureGuard weatherproofing boot on 4.1-9.5 Male side

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ1-50A

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Female
Interface, Connector B	4.1-9.5 DIN Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Cable Assembly Length Range (m)	1 – 15
Nominal Size	1/4 in

Jumper Assembly Sample Label

F1A-HFKM-P-W1



Environmental Specifications

- Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition
- Weatherproofing Method** HELIAX® SureGuard weatherproofing boot