

# 760254043 | EPX-1U-CHD-OPEN-FX



EPX 1U open fixed panel, accepts (8) CHD style modules, adapter packs, or splice cassettes, providing up to 48 duplex LC ports

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	EPX

## General Specifications

<b>Application</b>	Accepts eight CHD modular cassettes
<b>Color</b>	Black
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Module/Adapter Pack Slots, quantity</b>	4
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Fibers, quantity</b>	96
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	327.91 mm   12.91 in

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	1.057 kg   2.33 lb