

# MC-DPM35M-6-72

---



GroundSmart® Monopole Co-location Dual Pipe Mount Kit, 12 in to 50 in OD, 4 ft 9 in face, includes pipes

## Product Classification

**Product Type** Co-location dual pipe mount kit

## General Specifications

**Mounting** Monopole, 304.8–1270 mm (12–50 in) OD  
**Pipe, quantity** 6  
**Sectors, quantity** 3

## Dimensions

**Height** 1,828.8 mm | 72 in  
**Face Width** 1.463 m | 4.8 ft  
**Width** 1,447.8 mm | 57 in  
**Length** 355.6 mm | 14 in  
**Pipe Length** 1,828.8 mm | 72 in  
**Mounting Diameter, maximum** 1270 mm | 50 in  
**Mounting Diameter, minimum** 304.8 mm | 12 in  
**Pipe Outer Diameter** 88.9 mm | 3.5 in  
**Stand-off Distance** 355.6 mm | 14 in  
**Mounting Circumference, maximum** 3,990.34 mm | 157.1 in  
**Mounting Circumference, minimum** 1,196.34 mm | 47.1 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC  
**Wind Rating Criteria** Two 72 in x 8 in panel antennas per sector

# MC-DPM35M-6-72

---

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Dual pipe frames | Pipe mounts | Ring mount

**Packaging quantity** 1

**Weight, net** 376.482 kg | 830 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code