

7830351 | CWDM Add/Drop Multiplexer, 1591-1611 nm



CWDM Fiber Optical Module, Add/Drop Multiplexer, 1591-1611 nm, LC /PC, 2 channels

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Product Type | CWDM module |
| Product Series | LGX |

General Specifications

| | |
|----------------------|-----------------------|
| Device Type | Coupler Splitter |
| Functionality | Add/drop for 2 fibers |

Dimensions

| | |
|---------------|-------------------|
| Height | 10 mm 0.394 in |
| Width | 100 mm 3.937 in |
| Depth | 80 mm 3.15 in |

Packaging and Weights

| | |
|-----------------------|--------------------|
| Height, packed | 45 mm 1.772 in |
| Width, packed | 400 mm 15.748 in |
| Depth, packed | 155 mm 6.102 in |
| Weight, gross | 0.16 kg 0.353 lb |
| Weight, net | 0.06 kg 0.132 lb |