


FPCH-33YZ



Fiber Optic Patch Cord, singlemode, 1.2 mm LSZH jacket, duplex, LC/APC-LC/APC, yellow. tuned

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Europe Latin America Middle East/Africa North America |
| Product Type | Fiber patch cord, duplex |
| Product Series | FPCH |

General Specifications


| | |
|---------------------------------------|---------------------|
| Connector A, quantity | 2 |
| Color, boot A | Green |
| Color, connector A | Green |
| Connector B, quantity | 2 |
| Color, boot B | Green |
| Color, connector B | Green |
| Interface, Connector A | LC/APC |
| Interface Feature, connector A | Grade B performance |
| Interface, Connector B | LC/APC |
| Interface Feature, connector B | Grade B performance |
| Jacket Color | Yellow |
| Total Fibers, quantity | 2 |

Dimensions

| | |
|-----------------------------|-------------------|
| Diameter Over Jacket | 1.2 mm 0.047 in |
|-----------------------------|-------------------|

Ordering Tree

FPCH-33YZ



Optical Specifications

| | |
|---|-------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A2/B2 |
| Insertion Loss, maximum, connector A | 0.25 dB |
| Insertion Loss, maximum, connector B | 0.25 dB |
| Return Loss, minimum, connector A | 65 dB |
| Return Loss, minimum, connector B | 65 dB |

Environmental Specifications

| | |
|----------------------------|-------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |



FPCH-33YZ

Included Products

760243025 - 1.2 mm LSZH Simplex Cable
POC-FO-CAB-SX-8G-1.2MM-YL