

# C300-NFSM-M3

---

CNT-300A CNT® Jumper with interface types N Female and SMA Male, 0.3m



## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-300

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	CNT-300
<b>Interface, Connector A</b>	N Female
<b>Interface, Connector B</b>	SMA Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	0.3 m   0.984 ft
<b>Nominal Size</b>	0.300 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–2000 MHz	1.222	20
2000–3000 MHz	1.288	18

## Jumper Assembly Sample Label

# C300-NFSM-M3

---

