

A7818471 | Optical Multiplexer, 4 channels



CWDM Fiber Optical Module, Mux, 1550-1610 nm, LC/PC, 4 channels

- Trade Agreements Act (TAA) compliant

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | CWDM module |
| Product Series | LGX |

General Specifications

| | |
|----------------------|----------------|
| Device Type | Plug-in module |
| Functionality | Multiplexing |

Dimensions

| | |
|---------------|-------------------|
| Height | 29 mm 1.142 in |
| Width | 130 mm 5.118 in |
| Depth | 185 mm 7.283 in |

Packaging and Weights

| | |
|-----------------------|--------------------|
| Height, packed | 65 mm 2.559 in |
| Width, packed | 275 mm 10.827 in |
| Depth, packed | 160 mm 6.299 in |
| Weight, gross | 0.5 kg 1.102 lb |
| Weight, net | 0.4 kg 0.882 lb |