

# A7818479 | Optical Demultiplexer, 18 channels



CWDM Fiber Optical Module, Demux, 1270-1610 nm, LC/PC, 18 channels

- Trade Agreements Act (TAA) compliant

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | CWDM module   |
| <b>Product Series</b>        | LGX   |

## General Specifications

|                      |                |
|----------------------|----------------|
| <b>Functionality</b> | Demultiplexing |
|----------------------|----------------|

## Dimensions

|               |                    |
|---------------|--------------------|
| <b>Height</b> | 44 mm   1.732 in   |
| <b>Width</b>  | 483 mm   19.016 in |
| <b>Depth</b>  | 290 mm   11.417 in |

## Packaging and Weights

|                       |                    |
|-----------------------|--------------------|
| <b>Height, packed</b> | 90 mm   3.543 in   |
| <b>Width, packed</b>  | 548 mm   21.575 in |
| <b>Depth, packed</b>  | 345 mm   13.583 in |
| <b>Weight, gross</b>  | 2.1 kg   4.63 lb   |
| <b>Weight, net</b>    | 1.7 kg   3.748 lb  |