



Constellation™ Transmitter Card, 600 W, fault managed power delivery card interface between the CPCX-12 and the power delivery cabling. Up to 24 can be loaded into the CPCX-12

Product Classification

Regional Availability	North America
Portfolio	SYSTIMAX®
Product Type	Power transmitter card
Product Brand	Constellation™

General Specifications

Color	Gray
Rack Units	1
Standards	CISPR 32 IEC/EN 55032 EN 300 386 v2.1.1 EN 50121-4 FCC Part 15B Class A

Dimensions

Height	14.48 mm 0.57 in
Width	38.2 mm 1.504 in
Depth	338.9 mm 13.343 in
Length	338.9 mm 13.343 in

Electrical Specifications

Output Current, maximum	3 A
Output Power, maximum	600 W
Output Voltage	336 Vdc

Material Specifications

Material Type	Molded plastic
----------------------	----------------

Environmental Specifications

Operating Temperature	-20 °C to +50 °C (-4 °F to +122 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

760254288 | CTX-6

Relative Humidity	5%–95%, non-condensing
Environmental Space	Indoor
Safety Standard	IEC 62368-1

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

