

WPB-FIXM-HS



HELIAX® SureGuard® Boot for 1/4 in jumpers to antennas or devices

Product Classification

Product Type	Weatherproofing boot
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Application	Provides additional moisture seal for cable connections
Applications per Kit	One 1/4 in to antenna or device connection
Color	Black

Dimensions

Width	18 mm 0.709 in
Length	75 mm 2.953 in
Cable Diameter for Seal, maximum	7.75 mm 0.305 in
Cable Diameter for Seal, minimum	6.99 mm 0.275 in
Inner Diameter	4.5 mm 0.177 in
Nominal Size	1/4 in

Material Specifications

Material Type	Silicone rubber
----------------------	-----------------

Environmental Specifications

Installation temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
UV Resistance Test Method	ASTM G154-12a
UV Resistance, minimum with no degradation	≥1000 hours

WPB-FIXM-HS

Weather Resistance Test Method IEC 60068-2-11 | IEC 60529:2001, IP68

Packaging and Weights

Height, packed	30 mm 1.181 in
Width, packed	120 mm 4.724 in
Length, packed	140 mm 5.512 in
Packaging quantity	1
Weight, gross	25 g 0.055 lb